



Summary

[Request a quote](#)

[Catalog](#)

| | |
|--------------------------------|---|
| Number of contacts Low Voltage | 16 |
| Gender | Standard |
| Socket / Receptacle | Socket / Receptacle - Fixed Panel Front Mounted |
| Locking system | Threaded |
| Size | 2W |
| Series | W - Underwater |

Technical details

Electrical Configuration

| | |
|---------------------------------|-------------------------|
| Contact Termination Low voltage | PCB - Straight |
| R (max) | 6.1 mOhm |
| Insert configuration value | 2W.316 - 16 Low Voltage |
| Rated current | 6 Amps |
| Contact Type | Print (straight) |
| Contact Dia. | 0.7 mm (0.028in) |
| Number of contacts Low Voltage | 16 |
| Gender | Standard |


https://www.lemo.com/int_en/solutions/supreme/w-underwater/evg-2w-316-cln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | EV - Fixed socket, nut fixing |
| Socket / Receptacle | Fixed Panel Front Mounted |
| Housing material | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system | Threaded |
| Keying | 1 key (alpha=0, Plug: male contacts, Receptacle: female contacts) |
| Weight | 25.45 g |

Drawings



Dimensions

| | A | B | e | e1 | E | L | N | S1 | S2 | S3 |
|-----|----------|----------|----------|-----------|----------|----------|----------|-----------|-----------|-----------|
| mm. | 22.5 | 21.8 | M16x1.0 | M20x1.0 | 9 | 30.7 | 9 | 14.5 | 18.5 | 19 |
| in. | 0.89 | 0.86 | | | 0.35 | 1.21 | 0.35 | 0.57 | 0.73 | 0.75 |

https://www.lemo.com/int_en/solutions/supreme/w-underwater/evg-2w-316-cln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.