



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	30
Wire Size/AWG	32 - 28
Gender	Standard
Plug	Plug - Fixed
Locking system	Snap-on
Size	3B
Suggested matching part	PHG.3B.330.CLLD10
Series	B - Indoor keyed

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fag-3b-330-cyb.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	30
Contact Termination Low voltage	Crimp
R (max)	6.1 mOhm
Insert configuration value	3B.330 - 30 Low Voltage
Insulator	Y: PEEK for crimp contacts
Rated current	3.5 A
Vtest (contact-contact)	2 kV (DC)
Vtest (contact-shell)	1.7 kV (DC)
Contact retention	22 N
Max. Conductor	0.09 mm ² (AWG 28)
Min. Conductor	0.035 mm ² (AWG 32)
Bucket Dia.	0.45 mm (0.018in)
Contact Dia.	0.7 mm (0.028in)
Wire Size/AWG	32 - 28
Gender	Standard

Form & Material

Shell style / Model id	FA - Fixed plug, non-latching, nut fixing
Plug	Fixed
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Snap-on
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	37.26 g

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fag-3b-330-cyb.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Drawings



Dimensions

	A	B	e	E	L	M	N	S1	S3
mm.	22	25.2	M18x1.0	5.8	32.1	17	30.2	16.5	22
in.	0.87	0.99		0.23	1.26	0.67	1.19	0.65	0.87

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fag-3b-330-cyb.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo

Accessories	
Replacement contact	FGG.3B.556.ZZC
Tools	
Spanner	DCA.91.282.2TN
Extraction tool	DCC.07.04B.LAG
Crimp tool	DPC.91.701.V