



## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	2
Wire Size/AWG	30 - 22
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	2.60 - 3.00 mm
Size	0E
Matching parts	<a href="#">ERA.0E.302.CLL</a>
Series	E - Outdoor Stepped Insert

## Technical details

### Electrical Configuration

Contact Termination Low voltage	Solder
R (max)	4.8 mOhm
Insert configuration value	0E.302 - 2 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	10 Amps
Vtest	1500 V (AC), 2100 V (DC)
Contact Type	Solder
Max. Solid Conductor	0.34 mm <sup>2</sup> (AWG 22)
Bucket Dia.	0.8 mm (0.031in)
Contact Dia.	0.9 mm (0.0354in)
Number of contacts Low Voltage	2
Wire Size/AWG	30 - 22

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/ffa-0e-302-clac30.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ffa-0e-302-clac30.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Form & Material

Shell style / Model id	FFA - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with male pin 1
Weight	12.43 g


## Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental protection (IP rating)	IP68
Minimal temperature	-55°C / +200°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	2.60 - 3.00 mm

## Drawings



[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/ffa-0e-302-clac30.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ffa-0e-302-clac30.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Dimensions

	<b>S2</b>	<b>M</b>	<b>A</b>	<b>L</b>
mm.	8	23	11	34
in.	0.31	0.91	0.43	1.34

## Recommended By Lemo







### Accessories

Compatible cap [BFA.0E.100.NAS](#)

### Tools

Spanner wrench [DCD.0E.ZZZ.PA080](#)

## Cables

<b>Cable PartNumber</b>	<b>Material</b>	<b>Colour</b>	<b>Cable image</b>
CMN.02.T28.030PGCE	PVC	GREY	
CMN.02.T28.030PGZE		grey	
CMN.02.T28.030PNCE	PVC	Black	
CMN.02.T28.030PNZE			
2050	PVC	Black	
2260	PTFE	White	

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/ffa-0e-302-clac30.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ffa-0e-302-clac30.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.