



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts High Voltage	1
Plug	Plug - Straight
Locking system	Push-pull
Size	3Y
Suggested matching part	<a href="#">ERA.3Y.425.CLL</a>
Series	Y - High Voltage Unipole

[https://www.lemo.com/int\\_en/solutions/supreme/y-high-voltage-unipole/ffr-3y-425-cfae55n.html](https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/ffr-3y-425-cfae55n.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts High Voltage	1
Contact Termination High voltage	Solder
Insert configuration value	3Y.425 - 1 High Voltage
Insulator	F: Silicon (LSR)/ Y series
Rated current	8 A
Test voltage (kV DC)	52
Creepage distance	25.5 mm

## Form & Material

Shell style / Model id	FFR - Straight plug for cable crimping with bend relief and safety locking ring
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular
Colour	Grey
Weight	100.1 g

## Environment

Technical domain	Specialties and Other
Environmental sealing (IP rating)	IP50
Salt Spray Corrosion	>1000 hr



## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Crimp

# Drawings

[https://www.lemo.com/int\\_en/solutions/supreme/y-high-voltage-unipole/ffr-3y-425-cfae55n.html](https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/ffr-3y-425-cfae55n.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



## Dimensions

	A	L	M	S1
mm.	19	120	92	15
in.	0.75	4.72	3.62	0.59

## Recommended By Lemo

### Accessories

Compatible cap	<a href="#">BRF.3K.200.NAS</a>
----------------	--------------------------------