



Summary

[Request a quote](#)

[Catalog](#)

Number of contacts High Voltage	1
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	4.20 - 5.20 mm
Size	1Y
Matching parts	ERA.1Y.405.CLL
Series	Y - High Voltage Unipole

Technical details

Electrical Configuration

Contact Termination High voltage	Solder
Insert configuration value	1Y.405 - 1 High Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	8 Amps
Test voltage (kV AC)	7.5
Contact Type	Solder
Creepage distance	16 mm
Number of contacts High Voltage	1

https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/ffa-1y-405-clac52.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Form & Material

Shell style / Model id	FFA - Straight plug with cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular
Weight	30.53 g



Environment

Technical domain	Specialties and Other
Environmental protection (IP rating)	IP50
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	4.20 - 5.20 mm

Drawings



Dimensions

	A	L	M	S1
mm.	13	54	27.5	9
in.	0.51	2.13	1.08	0.35

https://www.lemo.com/int_en/solutions/supreme/y-high-voltage-unipole/ffa-1y-405-clac52.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.