



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	4
Wire Size/AWG	22 - 14
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.80 - 7.20 mm
Size	3S
Suggested matching part	<a href="#">ERA.3S.304.CLL</a>
Series	S - Indoor Stepped Insert

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/ffa-3s-304-clac72z.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffa-3s-304-clac72z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	4
Contact Termination Low voltage	Solder
Insert configuration value	3S.304 - 4 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	18 A
Test voltage (kV DC)	2.1
Bucket Dia.	1.8
Contact Dia.	2
Wire Size/AWG	22 - 14

## Form & Material

Shell style / Model id	FFA - Straight plug, cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with male pin 1
Colour	Grey
Variant	Nut for fitting a bend relief
Weight	55.52 g

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/ffa-3s-304-clac72z.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffa-3s-304-clac72z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.80 - 7.20 mm

# Recommended By Lemo

## Accessories

Compatible cap	<a href="#">BFG.3B.100.PCSG</a>
----------------	---------------------------------




## Tools

Spanner	<a href="#">DCP.91.023.TN</a>
Spanner wrench	<a href="#">DCP.91.023.TN</a>

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/ffa-3s-304-clac72z.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffa-3s-304-clac72z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Cables

Cable PartNumber	Material	Colour	Cable image
240500	PVC	Grey	
240750	PVC	Grey	
417920	PVC	Grey	
CTR.75.030.121870G	PVC	Grey	

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/ffa-3s-304-clac72z.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffa-3s-304-clac72z.html)

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.