



Image for illustrative purpose only

## Summary

[Request a quote](#)

00and01Coaxial en

Nb of contacts Coax	1
Plug	Plug - Straight
Locking system	Push-pull
Size	1
Suggested matching part	<a href="#">ECP.01.250.DLL</a> <a href="#">PCS.01.250.DLLE31</a>

[https://www.lemo.com/int\\_en/ffs-01-250-dlae31.html](https://www.lemo.com/int_en/ffs-01-250-dlae31.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Nb of contacts Coax	1
Contact Termination Coax - Conductor fixing	Solder
Contact Termination Coax - Screen fixing	Crimp
Insert configuration value	01.250 - 1 Coax (50 Ohm)
Rated current	4 A
Impedance	50 Ohms

## Form & Material

Shell style / Model id	FFS - Straight plug for cable crimping
Plug	Straight
Housing material	Brass (gold plated [ISO 27874]) shell, collet nut, brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Weight	1.31 g


## Environment

Environmental sealing (IP rating)	IP50
Endurance	1000 mating cycles
Temperature range	-55°C / +230°C (max. temperature valid for short periods of use.)

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Crimp

# Drawings



[https://www.lemo.com/int\\_en/ffs-01-250-dlae31.html](https://www.lemo.com/int_en/ffs-01-250-dlae31.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Dimensions

	<b>A</b>	<b>S1</b>	<b>S2</b>	<b>L</b>	<b>M</b>
mm.	5	4	4	20	14.5
in.	0.2	0.16	0.16	0.79	0.57

[https://www.lemo.com/int\\_en/ffs-01-250-dlae31.html](https://www.lemo.com/int_en/ffs-01-250-dlae31.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.