



## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	9
Wire Size/AWG	34 - 28
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	3.60 - 4.00 mm
Size	0T
Matching parts	<a href="#">EGG.0T.309.CLL</a>
Series	T - Small Outdoor keyed

## Technical details

[https://www.lemo.com/int\\_en/solutions/originals/t-outdoor-keyed/fgg-0t-309-clac40.html](https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/fgg-0t-309-clac40.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Contact Termination Low voltage	Solder
R (max)	8.7 mOhm
Insert configuration value	T.309 - 9 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	2 Amps
Vtest (contact-contact)	600 V (AC), 850 V (DC)
Vtest (contact-shell)	500 V (AC), 710 V (DC)
Contact Type	Solder
Max. Solid Conductor	0.09 mm <sup>2</sup> (AWG 28)
Max. Stranded Conductor	0.09 mm <sup>2</sup> (AWG 28)
Bucket Dia.	0.45 mm (0.018in)
Contact Dia.	0.5 mm (0.02in)
Number of contacts Low Voltage	9
Wire Size/AWG	34 - 28
Gender	Standard

## Form & Material

Shell style / Model id	FG - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)



## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	3.60 - 4.00 mm

[https://www.lemo.com/int\\_en/solutions/originals/t-outdoor-keyed/fgg-0t-309-clac40.html](https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/fgg-0t-309-clac40.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Drawings



## Dimensions

	<b>A</b>	<b>L</b>	<b>M</b>	<b>S1</b>	<b>S2</b>
mm.	9.5	39	29	7.5	7
in.	0.37	1.54	1.14	0.3	0.28

[https://www.lemo.com/int\\_en/solutions/originals/t-outdoor-keyed/fgg-0t-309-clac40.html](https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/fgg-0t-309-clac40.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.