



Summary

[Request a quote](#)

[Catalog](#)

Low Voltage	1
Wire Size/AWG	20 - 18
Size	3B
Matching parts	EGG.3B.665.ZZM
Series	B - Indoor keyed

Technical details

Electrical Configuration

Contact Termination Low voltage	Crimp
Contact Dia.	1.3
Low Voltage	1
Wire Size/AWG	20 - 18

Form & Material

Shell style / Model id	FG - Male crimp contact, standard barrel
Housing material	Gold plated [ISO 27874] brass
Keying	No keying
Weight	0.69 g


https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-3b-565-zzc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental protection (IP rating)	No IP rating
Minimal temperature	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Cable fixation	
Cable termination protection	Standard back nut (no additional protection)

Drawings



No keying

Dimensions

	A	C
mm.	1.3	1.4
in.	0.05	0.06

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-3b-565-zzc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.