

## Summary

[Request a quote](#)

[Catalog](#)

Low Voltage	1
Locking system	Push-pull

## Technical details

### Electrical Configuration

Insert configuration value	0.113 - 1 Low Voltage
Insulator	T: PTFE
Rated current	8 Amps
Contact Dia.	1.3
Low Voltage	1

### Form & Material

Shell style / Model id	FTA - T-plug with two in line receptacles
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular (can rotate)
Weight	7.35 g

[https://www.lemo.com/int\\_en/fta-00-113-ctf.html](https://www.lemo.com/int_en/fta-00-113-ctf.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment


Environmental protection (IP rating)

IP50

Salt Spray Corrosion

>1000 hr

## Drawings



## Dimensions

	<b>L</b>	<b>I</b>	<b>H</b>	<b>A</b>
mm.	30	9.5	17.5	9
in.	1.18	0.37	0.69	0.35

[https://www.lemo.com/int\\_en/fta-00-113-ctf.html](https://www.lemo.com/int_en/fta-00-113-ctf.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.