

SUMMARY

Wires

| | |
|---------|---|
| Low | 0 |
| High | 0 |
| Coax | 0 |
| Triax | 0 |
| Quad | 0 |
| Fiber | 0 |
| Fluidic | 0 |

Image is for illustrative purpose only

Download

[Request a quote](#)

[Catalog](#)

| | |
|------------------|-------------------------|
| Series | 3S |
| Termination type | No contacts / Accessory |
| IP rating | 0 |
| Cable Ø | 6.10 - 7.00 mm |
| Matching parts | |
| Status | active |
| Alternative part | |

TECHNICAL DETAILS

Mechanics

| | |
|-------------------|--|
| Shell Style/Model | GSC*: Lead through with cable collet |
| Keying | No keying |
| Housing Material | Brass (nickel plated) shell, collet nut, latch sleeve and mid pieces |
| Cable Fixing | ∅ 6.1 - 7 mm |
| Variant | |
| Weight | 23.65 g |

Performance

| | |
|---------------|----------------------|
| Configuration | 3S.290 : no contacts |
| Insulator | |
| Rated Current | |

Others

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Temp (min / max): -55°C / +250°C
Humidity (max): <=95% [at 60 deg C / 140 F]
Vibration: 15 g [10 Hz - 2000 Hz]
Shock Resistance: 100 g [6 ms]
Salt Spray Corrosion: >1000 hr
Climatical Category: 50/175/21
Shielding (min): 75 dB (10 MHz)
Shielding (min): 40 dB (1 GHz)
IP Rating: 0

DRAWINGS

Draws

No keying

Dimensions

| | A | B | E | L | M | S1 | S2 | S3 | e |
|-----|------|------|------|------|------|-----|------|------|---------|
| mm. | 17 | 19.5 | 8.1 | 30 | 12 | â?? | 14 | 17 | M15x1.0 |
| in. | 0,67 | 0,77 | 0,32 | 1,18 | 0,47 | | 0,55 | 0,67 | |

RECOMMENDED BY LEMO

Tools

None

Cables

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

