



## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	7
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	1F
Matching parts	<a href="#">FGN.1F.307.CLC</a>
Series	F - Rugged Push-Pull

## Technical details

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/hen-1f-307-clnp.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/hen-1f-307-clnp.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Contact Termination Low voltage	PCB - Straight
R (max)	6.1 mOhm
Insert configuration value	1F.307 - 7 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	7 Amps
Vtest (contact-contact)	1450 V (AC), 2050 V (DC)
Vtest (contact-shell)	1450 V (AC), 2050 V (DC)
Contact Type	Print (straight)
Contact Dia.	0.7 mm (0.028in)
Number of contacts Low Voltage	7
Gender	Standard

## Form & Material

Shell style / Model id	HE - Fixed receptacle, nut fixing, for printed circuit (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and nut, other pieces brass
Locking system	Push-pull
Keying	3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts)
Variant	Watertight unmated (connector to device)
Weight	11.77 g


## Environment

Technical domain	Motorsport, Security and Defence
Environmental protection (IP rating)	IP68
Minimal temperature	-50°C / +150°C
Climatical Category	50/175/21 (Aluminium shell)
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Pressure	5 bars
Salt Spray Corrosion	>1000 hr

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/hen-1f-307-clnp.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/hen-1f-307-clnp.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Drawings



## Dimensions

	<b>A</b>	<b>B</b>	<b>e</b>	<b>E</b>	<b>H</b>	<b>L</b>	<b>M</b>	<b>P</b>	<b>S1</b>	<b>S2</b>	<b>X</b>
mm.	17	17	M13x0.75	3	7.62	21.5	3.2	14.5	11.5	14	17.5
in.	0.67	0.67		0.12	0.3	0.85	0.13	0.57	0.45	0.55	0.69

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/hen-1f-307-clnp.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/hen-1f-307-clnp.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.