

Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Coax	1
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Push-pull
Jacket cable outside diameter [mm]	3.10 - 3.50 mm
Size	0E
Suggested matching part	<a href="#">FFA.0E.250.CLAC35</a>
Series	E - Outdoor Stepped Insert

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/pca-0e-250-cllc35h.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/pca-0e-250-cllc35h.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Nb of contacts Coax	1
Contact Termination Coax	Solder
Insert configuration value	0E.250 - 1 Coax (50 Ohm)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	6 A
Impedance	50 Ohm
OHM	50
VSWR	1.02 + 0.25 * f/GHz
Vtest	3000 V (AC), 4200 V (DC)
Contact Type	Coaxial 50 Ohm (Solder)
Cable type	RG 178 B/U, RG 196 A/U, RG 188 A/U, RG 316 B/U, RG 174 A/U, HF-2114, RG 122 /U
Bucket Dia.	1 mm (0.039in)
Contact Dia.	0.9 mm (0.035in)

## Form & Material

Shell style / Model id	PCA - Free receptacle, cable collet
Socket / Receptacle	Free
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Circular, female
Colour	Grey
Variant	Viton O-Ring
Weight	14.6 g

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/pca-0e-250-cllc35h.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/pca-0e-250-cllc35h.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-20°C / +200°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	3.10 - 3.50 mm

## Drawings



## Dimensions

	<b>A</b>	<b>L</b>	<b>S2</b>
mm.	13	34	8
in.	0.51	1.34	0.31

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/pca-0e-250-cllc35h.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/pca-0e-250-cllc35h.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Recommended By Lemo

## Accessories

---

Compatible cap [BRF.0K.200.NAS](#)

## Tools

---

Spanner wrench [DCD.0E.ZZZ.PA080](#)

# Cables

Cable PartNumber	Material	Colour	Cable image
CCX.75.040.195327G	PVC	Grey	

---

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/pca-0e-250-cllc35h.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/pca-0e-250-cllc35h.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.