



## Summary

[Request a quote](#)

[Catalog](#)

Low Voltage	2
Wire Size/AWG	20 - 18
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	2.70 - 3.90 mm
Size	1P
Matching parts	<a href="#">PLG.M0.2GL.MG</a>
Series	REDEL P - Push-Pull

## Technical details

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pag-m0-2gl-cc39g.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m0-2gl-cc39g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Contact Termination Low voltage	Crimp
R (max)	3.5 mOhm
Insert configuration value	1P.M02 - 2 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	10 Amps
Test voltage (kV rms) Contact-contact	1.2
Contact retention	20 N
Contact Type	Crimp
Max. Conductor	1 mm <sup>2</sup> (AWG 18)
Min. Conductor	0.5 mm <sup>2</sup> (AWG 20)
Air clearance	1.52 mm
Creepage distance	1.52 mm
Bucket Dia.	1.4
Contact Dia.	1.3 mm (0.0512in)
Low Voltage	2
Wire Size/AWG	20 - 18
Gender	Standard

## Form & Material

Shell style / Model id	PA - Straight plug with cable collet
Plug	Straight
Housing material	PSU (Polysulfone), gray
Locking system	Push-pull
Keying	1 key (alpha=0, Plug: male contact, Receptacle: female contact)
Variant	Gray collet nut
Weight	5.75 g

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pag-m0-2gl-cc39g.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m0-2gl-cc39g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental protection (IP rating)	IP50
Minimal temperature	-50°C / +150°C
F ret (max)	150 N
F ret (min)	50 N
Steam sterilization	> 100 times (with potting on rear connection)

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	2.70 - 3.90 mm

## Drawings



## Recommended By Lemo

### Accessories

Replacement contact [SINGLE: FGG.5B.567.ZZC KIT OF 2: PAG.567.02C](#)

### Tools

Positionner [DCE.91.135.BVD](#)
















Extraction tool [DCF.133.5LT](#)

Crimp tool [DPC.91.701.V](#)

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pag-m0-2gl-cc39g.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m0-2gl-cc39g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Cables

Cable PartNumber	Material	Colour	Cable image
CMN.02.T28.030PGCE	PVC	GREY	
CMN.02.T28.030PGZE		grey	
CMN.02.T28.030PNCE	PVC	Black	
CMN.02.T28.030PNZE			
20140	PVC	Grey	
20140	PVC	Grey	
20141	PVC	Grey	
20142	PVC	Red	
20143	PVC	Green	
20144	PVC	Black	
20145	PVC	Yellow	
20146	PVC	Black	
20240	PTFE	White	
2050	PVC	Black	
2080	PVC	Grey	
2260	PTFE	White	

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pag-m0-2gl-cc39g.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m0-2gl-cc39g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.