



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

| | |
|--------------------------------|-------------------------------|
| Number of contacts Low Voltage | 8 |
| Wire Size/AWG | 32 - 24 |
| Gender | Standard |
| Plug | Plug - Straight |
| Locking system | Push-pull |
| Size | 1P |
| Suggested matching part | PLG.M0.8GL.LG |
| Series | REDEL P - Push-Pull |

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m0-8gl-azzzg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|---------------------------------|-------------------------------|
| Number of contacts Low Voltage | 8 |
| Contact Termination Low voltage | Solder |
| R (max) | 6.5 mOhm |
| Insert configuration value | 1P.M08 - 8 Low Voltage |
| Insulator | L: PEEK (UL 94 / V-0/1.5) |
| Rated current | 5 A |
| Test voltage contact-contact | 1.48 (kV DC) |
| Max. Solid Conductor | 0.25 mm ² (AWG 24) |
| Max. Stranded Conductor | 0.14 mm ² (AWG 26) |
| Air clearance | 0.6 mm |
| Creepage distance | 0.6 mm |
| Bucket Dia. | 0.6 mm (0.024in) |
| Contact Dia. | 0.7 mm (0.0275in) |
| Wire Size/AWG | 32 - 24 |
| Gender | Standard |

Form & Material

| | |
|------------------------|--|
| Shell style / Model id | PA - Straight plug with cable collet |
| Plug | Straight |
| Housing material | PSU (Polysulfone), grey |
| Locking system | Push-pull |
| Keying | G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts) |
| Colour | Grey |
| Variant | Grey collet nut |
| Weight | 4.69 g |

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m0-8gl-azzzg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Environment

| | |
|-----------------------------------|---|
| Technical domain | Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental sealing (IP rating) | IP50 |
| Endurance | > 5000 mating cycles |
| Temperature range | -50°C / +150°C |
| F ret (max) | 150 N |
| F ret (min) | 50 N |
| Steam sterilization | Fully sterilizable (Steam, Gamma, ETO) following our protocols and tests in line with ISO 11134 and IEC 60601-1 standards. For more details on sterilization methods and cycles, please contact us. |

Cable fixation

| | |
|------------------------------|--|
| Cable termination protection | Standard back nut (no additional protection) |
| Fixation type | Cable collet |

Drawings



https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m0-8gl-azzzg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.