



## Summary

[Request a quote](#)

[Catalog](#)

Low Voltage	7
Wire Size/AWG	30 - 22
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Push-pull
Jacket cable outside diameter [mm]	8.60 - 9.50 mm
Size	3P
Matching parts	<a href="#">FGG.3P.306.NLXD95</a>
Series	REDEL P - Push-Pull

## Technical details

### Electrical Configuration

Insert configuration value	3P.306 - 6 Low Voltage + 1 Ground contact
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	6 Amps
Contact Dia.	0.9
Low Voltage	7
Wire Size/AWG	30 - 22

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/phg-3p-306-nlxd95g.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/phg-3p-306-nlxd95g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Form & Material

Shell style / Model id	PH - Free receptacle, cable collet
Socket / Receptacle	Free
Housing material	PSU (Polysulfone), black
Locking system	Push-pull
Keying	User configurable, 1 of 11 key positions. Plug: male contacts, Receptacle: female contacts



## Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental protection (IP rating)	IP61
Minimal temperature	-50°C / +150°C
F ret (max)	200 N
F ret (min)	100 N
Steam sterilization	20 times (with potting on rear connection)

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	8.60 - 9.50 mm

## Drawings



## Dimensions

	L	A
mm.	55	27
in.	2.17	1.06

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/phg-3p-306-nlxd95g.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/phg-3p-306-nlxd95g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.