



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	4
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	1P
Suggested matching part	<a href="#">PAG.M0.4SL.AC52RZ</a>
Series	REDEL P - Push-Pull

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pkg-m0-4sl-nr.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pkg-m0-4sl-nr.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Contact Termination Low voltage	PCB - Straight
R (max)	4.5 mOhm
Insert configuration value	1P.M04 - 4 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	8 A
Test voltage contact-contact	1.7 (kV DC)
Contact Type	Print (straight)
Air clearance	1.2 mm
Creepage distance	1.2 mm
Contact Dia.	0.9 mm (0.0354in)
Number of contacts Low Voltage	4
Gender	Standard

## Form & Material

Shell style / Model id	PK - Fixed receptacle with two nuts (back panel mounting), straight print contacts
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	PEI (Polyetherimide), gray
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey - Red
Variant	Red front nut
Weight	4.85 g

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pkg-m0-4sl-nr.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pkg-m0-4sl-nr.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

---

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	> 5000 mating cycles
Temperature range	-50°C / +170°C
F ret (max)	150 N
F ret (min)	50 N
Steam sterilization	Fully sterilizable (Steam, Gamma, ETO) following our protocols and tests in line with ISO 11134 and IEC 60601-1 standards. For more details on sterilization methods and cycles, please contact us.

---

## Cable fixation

---

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet

---

# Recommended By Lemo

## Accessories

---

Compatible cap [PBG.200.BMV](#)

## Tools

---

Spanner [POB.186.GN](#)

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pkg-m0-4sl-nr.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pkg-m0-4sl-nr.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.