

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

[M series](#)

[Application leaflet Security Defence](#)

Number of contacts Low Voltage	66
Wire Size/AWG	26 - 22
Gender	Reverse Gender
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Ratchet
Jacket cable outside diameter [mm]	14.25 - 28.50 mm
Size	5M
Suggested matching part	FBX.5M.366.XRY44
Series	M - Rugged Ratchet coupling

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/phx-5m-366-xrwt44.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	66
Contact Termination Low voltage	Crimp
Insert configuration value	5M.366_44 - 44 (0.7 mm) + 22 (1.3 mm) Low Voltage
Insulator	R: PEEK (mixed multipole)
Rated current	0.7 mm : 3 A, 1.3 mm : 6 A
Test voltage (kV rms) Contact-contact	0.7 mm : 1.65 kV, 1.3 mm : 1.95 kV
Test voltage (kV rms) Contact-shell	0.7 mm : 2.70 kV, 1.3 mm : 1.80 kV
Bucket Dia.	44x0.87 mm, 22x1.6 mm
Contact Dia.	44x0.7 mm, 22x1.3 mm
Wire Size/AWG	26 - 22
Gender	Reverse Gender

Form & Material

Shell style / Model id	PH - Free receptacle with arctic grip and mold stop
Socket / Receptacle	Free
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Ratchet
Keying	X: 5 keys (alpha=100, beta=125, gamma=40, delta=20, plug: female contacts, receptacle: male contacts)
Colour	Grey
Weight	44.26 g

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/phx-5m-366-xrwt44.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Environment

Technical domain	Motorsport, Security and Defence, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP68
Endurance	3000 mating cycles
Temperature range	-20°C / +200°C (max. temperature valid for short periods of use.)
EMI Shielding EIA 364-66A	≥ 80 dB (1 GHz), ≥ 70 dB (3 GHz), ≥ 58 dB (6 GHz), ≥ 40 dB (10 GHz)
Gunfire vibration	25 Hz - 2000 Hz, 3 axis (Apache helicopter)
Humidity (max)	21 days at 95%
Lighting strike EIA 364-76	10K amps - 6 times
Shock Resistance	300 g [3 ms]
Thermal shock	5 cycles: -65°C to +150°C
Vibration-Random	37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]
Vibration-Sine	30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 48 hr

Cable fixation

Cable termination protection	For overmolding
Fixation type	Mold stop (overmolding)
Jacket cable outside diameter [mm]	14.25 - 28.50 mm

Drawings



https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/phx-5m-366-xrwt44.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Dimensions

	A	B	C	D	F	Ls	Lr	M	P	X
mm.	34.9	29.7	33.5	28.5	31.4	31.2	31.2	10.6	7.9	7.6
in.	1.37	1.17	1.32	1.12	1.24	1.23	1.23	0.42	0.31	0.3

Recommended By Lemo

Accessories

Replacement contact [FGN.0M.555.44C](#)

Compatible cap [BGF.5M.200.XAZ](#)

Tools

Positionner [DCE.91.070.5MVC](#)

Positionner 2 [DCE.91.130.5MVG](#)

Extraction tool [DCC.07.04B.LAG](#)

Extraction tool 2 [DCC.13.15B.LAG](#)

Crimp tool [DPC.91.701.V](#)

CAD

Documents

PCB [Download](#)

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/phx-5m-366-xrwt44.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.