



## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	4
Wire Size/AWG	12 - 10
Gender	Reverse Gender
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	12.60 - 13.50 mm
Size	5K
Series	K - Outdoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/pkl-5k-304-ylcc13.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/pkl-5k-304-ylcc13.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Contact Termination Low voltage	Crimp
R (max)	2.8 mOhm
Insert configuration value	5K.304 - 4 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	35 A
Vtest (contact-contact)	3200 V (AC), 4530 V (DC)
Vtest (contact-shell)	2400 V (AC), 3390 V (DC)
Contact retention	90 N
Contact Type	Crimp
Max. Conductor	6 mm <sup>2</sup> (AWG 10)
Min. Conductor	4 mm <sup>2</sup> (AWG 12)
Bucket Dia.	4 mm (0.157in)
Contact Dia.	4 mm (0.157in)
Number of contacts Low Voltage	4
Wire Size/AWG	12 - 10
Gender	Reverse Gender

## Form & Material

Shell style / Model id	PK - Fixed receptacle, nut fixing, cable collet
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Special housing (see notes for details)
Locking system	Push-pull
Keying	2 keys (gamma=75, plug: female contacts, receptacle: male contacts)
Weight	546.52 g

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/pkl-5k-304-ylcc13.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/pkl-5k-304-ylcc13.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	12.60 - 13.50 mm

## Drawings



## Dimensions

	<b>A</b>	<b>B</b>	<b>e</b>	<b>E</b>	<b>L</b>	<b>M</b>	<b>S1</b>	<b>S2</b>
mm.	55	54	M45x1.5	15	98	9	42.5	30
in.	2.17	2.13		0.59	3.86	0.35	1.67	1.18

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/pkl-5k-304-ylcc13.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/pkl-5k-304-ylcc13.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.