



Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	8
Wire Size/AWG	32 - 24
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	1.00 - 12.60 mm
Size	1P
Suggested matching part	<a href="#">PAB.M0.8GL.AC39J</a>
Series	REDEL P - Push-Pull

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/plb-m0-8gl-lj.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/plb-m0-8gl-lj.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	8
Contact Termination Low voltage	Solder
R (max)	6.5 mOhm
Insert configuration value	1P.M08 - 8 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	5 A
Test voltage contact-contact	1.48 (kV DC)
Max. Solid Conductor	0.25 mm <sup>2</sup> (AWG 24)
Max. Stranded Conductor	0.14 mm <sup>2</sup> (AWG 26)
Air clearance	0.6 mm
Creepage distance	0.6 mm
Bucket Dia.	0.6 mm (0.024in)
Contact Dia.	0.7 mm (0.0275in)
Wire Size/AWG	32 - 24
Gender	Standard

## Form & Material

Shell style / Model id	PL - Fixed receptacle, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	PSU (Polysulfone), grey
Locking system	Push-pull
Keying	B: 2 keys (alpha=60, Plug: male contacts, Receptacle: female contacts)
Colour	Grey - Yellow
Variant	Yellow front nut
Weight	4.9 g

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/plb-m0-8gl-lj.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/plb-m0-8gl-lj.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	> 5000 mating cycles
Temperature range	-50°C / +150°C
F ret (max)	150 N
F ret (min)	50 N
Steam sterilization	Fully sterilizable (Steam, Gamma, ETO) following our protocols and tests in line with ISO 11134 and IEC 60601-1 standards. For more details on sterilization methods and cycles, please contact us.

## Cable fixation

Jacket cable outside diameter [mm]	1.00 - 12.60 mm
------------------------------------	-----------------

# Recommended By Lemo











## Accessories

Compatible cap	<a href="#">PBG.200.BMV</a>
----------------	-----------------------------

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/plb-m0-8gl-lj.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/plb-m0-8gl-lj.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Cables

Cable PartNumber	Material	Colour	Cable image
CMN.08.T26.042QGZE	TPR (medical)	Grey	
108240	PTFE	White	
108260	PTFE	White	
16080	PVC	Grey	
180260	PVC	Black	
280250	PVC	Grey	
335990	PVC	Black	
335991	PVC	Black	
42265	PVC	Yellow	
80140	PVC	Grey	
8050	PVC	Black	
8280	PVC	Black	

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/plb-m0-8gl-lj.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/plb-m0-8gl-lj.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.