



Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	13
Wire Size/AWG	30 - 22
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	1.00 - 12.60 mm
Size	SP
Suggested matching part	<a href="#">SAN.M13.GLA.6B</a>
Series	REDEL SP - Inner Push-Pull

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/skn-m13-gllb.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/skn-m13-gllb.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	13
Contact Termination Low voltage	Solder
R (max)	6.5 mOhm
Insert configuration value	SP.M13 - 13 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	4 A
Test voltage contact-contact	1.5 (kV DC)
Max. Solid Conductor	0.34 mm <sup>2</sup> (AWG 22)
Max. Stranded Conductor	0.34 mm <sup>2</sup> (AWG 22)
Air clearance	0.5 mm
Creepage distance	0.5 mm
Bucket Dia.	0.8 mm (0.032in)
Contact Dia.	0.7 mm (0.028in)
Wire Size/AWG	30 - 22
Gender	Standard

## Form & Material

Shell style / Model id	SK_.SP - Fixed socket, key (N) or keys (P, S and T), with two nuts (back panel mounting), white front nut
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Proprietary sulfone, grey
Locking system	Push-pull
Keying	3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Colour	Grey - White
Variant	White front nut
Weight	4.45 g

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/skn-m13-gllb.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/skn-m13-gllb.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



## Environment

Technical domain	Medical
Environmental sealing (IP rating)	IP50
Endurance	>5000 mating cycles
Temperature range	-50°C / +170°C
Steam sterilization	> 100 times

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Jacket cable outside diameter [mm]	1.00 - 12.60 mm

## Drawings



## Dimensions

	a	B	N	e	E <sub>max</sub>
mm.	2.2	18.5	23.5	M14x1	8.5
in.	0.09	0.73	0.93		0.33

## Cables

Cable PartNumber	Material	Colour	Cable image
CMN.13.T22.072QGZE	TPR (medical)	Grey	

[https://www.lemo.com/int\\_en/solutions/redel/redel-sp-inner-push-pull/skn-m13-gllb.html](https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/skn-m13-gllb.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.