

## Summary

[Request a quote](#)

[Catalog](#)

Fluidic	1
Low Voltage	10
Wire Size/AWG	30 - 22
Gender	Standard
Locking system	Push-pull
Size	2P
Matching parts	<a href="#">CFB.P15.GLA.C72GZ</a>
Series	REDEL P - Push-Pull

## Technical details

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/cnb-p15-gllg.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/cnb-p15-gllg.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Fluidic	1
Insert configuration value	2P.P15 - 1 Fluidic with valve, 10 Low V.
Insulator	L: PEEK for solder contacts
Rated current	6 Amps
Test voltage (kV rms) Contact-contact	1.15
Air clearance	0.9 mm
Creepage distance	0.9 mm
Contact Dia.	0.7
Low Voltage	10
Wire Size/AWG	30 - 22
Gender	Standard

## Form & Material

Housing material	PSU (Polysulfone), gray
Locking system	Push-pull
Keying	3 keys (alpha=0, gamma=60, Plug: male contacts, Receptacle: female contacts)
Weight	5.22 g



## Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental protection (IP rating)	IP66
Minimal temperature	-50°C / +150°C

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

## Drawings



[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/cnb-p15-gllg.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/cnb-p15-gllg.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.