



Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	4.10 - 5.00 mm
Size	1D
Suggested matching part	<a href="#">ERN.1D.694.CNA</a>

# Technical details

## Electrical Configuration

Nb of contacts Quadrax	1
Contact Termination Quadrax	Solder
Insert configuration value	1D.694 - 1 Quadrax
Insulator	N: PBT
Rated current	0.5 A
Vtest (contact-contact)	420 V (AC), 600 V (DC)
Vtest (contact-shell)	420 V (AC), 600 V (DC)

## Form & Material

Shell style / Model id	FFA - Straight plug, cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts)
Variant	Nut for fitting a bend relief
Weight	16.19 g

## Environment

Technical domain	Security and Defence, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	1000 mating cycles
Temperature range	-40°C / +120°C
Insulating res.	10e11 Ohms
Shielding (min)	70dB (10 MHz)
Salt Spray Corrosion	>1000 hr



[https://www.lemo.com/int\\_en/ffa-1d-694-cnld52z.html](https://www.lemo.com/int_en/ffa-1d-694-cnld52z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	4.10 - 5.00 mm

Drawings



Dimensions

	A	L	M
mm.	12	42	33
in.	0.47	1.65	1.3