



## Summary

[Request a quote](#)

[Catalog](#)

[See video assembly instructions](#)

Number of contacts Low Voltage	10
Wire Size/AWG	24 - 20
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.30 - 14.00 mm
Size	2F
Matching parts	<a href="#">EGN.2F.310.CLM</a>
Series	F - Rugged Push-Pull

## Technical details

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/fgn-2f-310-clc.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-2f-310-clc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Contact Termination Low voltage	Crimp
R (max)	4.8 mOhm
Insert configuration value	2F.310 - 10 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	8 Amps
Vtest (contact-contact)	1800 V (AC), 2550 V (DC)
Vtest (contact-shell)	2100 V (AC), 2970 V (DC)
Contact retention	30 N
Contact Type	Crimp
Max. Conductor	0.5 mm <sup>2</sup> (AWG 20)
Min. Conductor	0.25 mm <sup>2</sup> (AWG 24)
Bucket Dia.	1.1 mm (0.043in)
Contact Dia.	0.9 mm (0.035in)
Number of contacts Low Voltage	10
Wire Size/AWG	24 - 20
Gender	Standard

## Form & Material

Shell style / Model id	FG - Straight plug
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and nut, other pieces brass
Locking system	Push-pull
Keying	3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts)
Weight	16.84 g

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/fgn-2f-310-clc.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-2f-310-clc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Environment

Technical domain	Motorsport, Security and Defence
Environmental protection (IP rating)	IP67
Minimal temperature	-55°C / +200°C
Climatical Category	50/175/21 (Aluminium shell)
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	Heatshrink
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.30 - 14.00 mm

## Drawings



## Dimensions

	M	A	B	L	X
mm.	17.9	17	14	27.8	8
in.	0.7	0.67	0.55	1.09	0.31

## Recommended By Lemo

### Accessories

Replacement contact [FGG.0B.560.ZZC](#)

### Tools

Positionner [DCE.91.090.BVC](#)












Extraction tool [DCC.09.05B.LAG](#)

Crimp tool [DPC.91.701.V](#)

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/fgn-2f-310-clc.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-2f-310-clc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Cables

Cable PartNumber	Material	Colour	Cable image
CMN.10.T20.080PGZE		grey	
CMN.10.T20.080PNZE			
CMN.10.T20.080QGC	TPR	Grey	
CMN.10.T22.068QGZE	TPR (medical)	Grey	
CMN.10.T28.053QGZE	TPR (medical)	Grey	
110220	PVC	Black	
110240	PTFE	White	
110280	PVC	Black	
210140	PVC	Grey	
210240	PVC	Black	
210250	PVC	Grey	
210260	PVC	Black	

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/fgn-2f-310-clc.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-2f-310-clc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.