



## Summary

[Request a quote](#)[Catalog](#)

Triax	1
Locking system	Push-pull
Size	4M

## Technical details

### Electrical Configuration

Triax	1
Insert configuration value	4M.675 - 1 Triax (75 Ohm)
Insulator	T: PTFE
Rated current	15 Amps
Impedance	75 Ohm
Vtest	1500 V (AC), 2120 V (DC)

### Form & Material

Shell style / Model id	RMA - Straight coupler
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Weight	146.33 g

[https://www.lemo.com/int\\_en/rma-4m-675-ctm.html](https://www.lemo.com/int_en/rma-4m-675-ctm.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Environment

Technical domain	Motorsport, Security and Defence, Transportation, Aerospace and UAV
Environmental protection (IP rating)	IP66
Climatical Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	85 dB (10 MHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

## Drawings



## Dimensions

	A	L
mm.	30	57
in.	1.18	2.24

[https://www.lemo.com/int\\_en/rma-4m-675-ctm.html](https://www.lemo.com/int_en/rma-4m-675-ctm.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.